



# Product data sheet

Power tools for trade & industry

Cordless Caulk Gun

## GCG 18V-600



Bosch's 1st Cordless Caulk Gun: 100% compatible with all Bosch Professional 18 V batteries

### The most important data

Battery voltage	18 V
Push Force	3.5 kN
Capacity Cartridges	310 ml, 400 ml

**Part Number** 0 601 9C4 001

[> More product information](#)

## Technical data

### Technical data

Battery voltage	18 V
Push Force	3.5 kN
Capacity Cartridges	310 ml, 400 ml
Capacity Sachets	400 ml, 600 ml
Feed rate	8 mm/sec
Weight excl. battery	2.2 kg
Packaging dimensions (width x length x height)	355 x 730 x 90 mm
Weight incl. battery	3.6 kg



# Product data sheet

Power tools for trade & industry

---

## Advantages:

- Easy control of material flow: Speed selection with 9 speed settings and variable speed trigger
- Fast working progress even with high viscosity adhesives: 3.5 kN push force combined with a maximum (no load) feed of 8 mm/sec
- No dripping or material overflow: Plunger rod auto-reverse function relieves pressure when trigger is released

