

Integral Black USB



8 GB

16 GB

32 GB

64 GB

128 GB

INTRODUCTION

Carry your data in style with the Integral Black USB Flash Drive. The Black USB is a fantastic value Flash Drive, with a compact, durable casing.

	LENGTH	WIDTH	DEPTH	WEIGHT
PRODUCT	54mm	18mm	8mm	10.1g
PACKED	170mm	105mm	13mm	26g

FEATURES

- Cap stores on base when drive is in use
- Hi-Speed USB 2.0

PRODUCT TYPE

USB Flash Drive

INTERFACE TYPE

Hi-Speed USB

INTERFACE CONNECTIVITY

1x Hi-Speed USB - 4 Pin USB Type A

COMPATIBILITY

Windows Vista, 7, 8.1 and 10
Mac OS 09 and Later.
Linux v2.4.0 and above.

ENVIRONMENTAL PARAMETERS

Min Operating Temperature 0°C
Max Operating Temperature 70°C

COMPLIANT STANDARD

Plug and Play

CAPACITY	PART CODE	BARCODE (EAN)
8GB	INFD8GBBLK.	5055288427532
16GB	INFD16GBBLK.	5055288427549
32GB	INFD32GBBLK.	5055288427556
64GB	INFD64GBBLK.	5055288427563
128GB	INFD128GBBLK	5055288432918

This device should not be used as your sole backup.

Product design and specification subject to change or modification without notice. E&OE.

All trademarks acknowledged.

2 year warranty

For warranty information please visit www.integralmemory.com/warranty