

2MP 1080P HD 4-in-1 Hybrid CCTV Bullet Security Camera's

- 3.6mm Fixed lens
- Upto 25M IR distance
- IP67 metal housing
- In-line output selector switch
- BNC/DC Connections



* Factory set in AHD format @ 2MP 1080P / 25fps resolution.

SPECIFICATION	
Model NO.	DFR36 (White Housing) DFR37 (Grey Housing)
Video Output Mode	AHD / TVI / CVI: 2MP (1080P) @ 25fps/30fps , 4MP @ 25fps/30fps CVBS: PAL / NTSC
Camera	
Image Sensor	1/3" CMOS sensor
Image Resolution	2MP: 1920x1080 (1080P) , 4MP: 2560x1440 (1440P)
TV System	PAL/NTSC
Electronic Shutter	AUTO
Scanning System	Progressive Scan
Lens	
Focus Length	3.6mm
Focus Control	Fixed
Lens Type	Fixed
Night Vision	
IR Cut Filter	YES
Infrared LED	14μ x 20PCS
Infrared Distance	25M
IR Status	AGC Auto Control
Camera Features	
Starlight	/
Day/Night	YES
OSD Menu	YES
WDR	DWDR
UTC	YES
Noise Reduction	DNR
White Balance	AUTO / MANUAL
Gain Control	AUTO
General	
Housing	Metal, IP67
Bracket	YES
Operation Temperature	-10°C ~ +60°C RH95% Max
Storage Temperature	-20°C ~ +60°C RH95% Max
Power Source	DC12V±10%, 700mA
Dimension	157(W) x 70(H) x 66(D)mm
Weight	650g