

5MP HD 4-in-1 Hybrid CCTV Bullet Security Camera's

- 3.6mm Fixed lens
- Upto 25M IR distance
- IP67 metal housing
- In-line output selector switch
- BNC/DC Connections



* Factory set in AHD format @ 5MP / 12.5fps resolution.

SPECIFICATION		
Model NO.	DFR38 (White Housing)	DFR39 (Grey Housing)
Video Output Mode	AHD / TVI: 5MP @ 20fps/12.5fps , 4MP @ 30fps/25fps/15fps , 2MP @ 30fps/25fps CVI: 4MP @ 30fps/25fps , 2MP @ 30fps/25fps CVBS: PAL / NTSC	
Camera		
Image Sensor	1/2.5" CMOS sensor	
Image Resolution	5MP: 2592 x 1944 , 4MP: 2560 x 1440 , 2MP: 1920 x 1080 (1080P)	
TV System	PAL/NTSC	
Electronic Shutter	AUTO	
Scanning System	Progressive Scan	
Lens		
Focus Length	3.6mm	
Focus Control	Fixed	
Lens Type	Fixed	
Night Vision		
IR Cut Filter	YES	
Infrared LED	14μ x 20PCS	
Infrared Distance	25M	
IR Status	AGC Auto Control	
Camera Features		
Starlight	/	
Day/Night	YES	
OSD Menu	YES	
WDR	DWDR	
UTC	YES	
Noise Reduction	DNR	
White Balance	AUTO / MANUAL	
Gain Control	AUTO	
General		
Housing	Metal, IP67	
Bracket	YES	
Operation Temperature	-10°C ~ +60°C RH95% Max	
Storage Temperature	-20°C ~ +60°C RH95% Max	
Power Source	DC12V±10%, 700mA	
Dimension	157(W) x 70(H) x 66(D)mm	
Weight	650g	