

Product Data Sheet for KleenGuard® G40 Polyurethane Coated Gloves - Hand-Specific Pairs / Black

### Product Information

<b>Customer Facing Code</b>	13837 - 13841
<b>Description</b>	KleenGuard® G40 Polyurethane Coated Gloves - Hand-Specific Pairs / Black
<b>PDS Reference</b>	15/07/2020
<b>Status</b>	On Sale

### Packaging Configuration

<b>Case Contents</b>	13837: 5 Bags x 12 Pairs = 60 Pairs 13838: 5 Bags x 12 Pairs = 60 Pairs 13839: 5 Bags x 12 Pairs = 60 Pairs 13840: 5 Bags x 12 Pairs = 60 Pairs 13841: 5 Bags x 12 Pairs = 60 Pairs
<b>Outer Pack Material</b>	Corrugated

### Packaging and Palletisation

Code/Size	ITF Barcode	EAN Barcode	Case LWH (cm)	Net/Gross Weight (kg)	Pallet Type	Pallet LWH (m)	Cases per Pallet	Inner Gross Weight (Kg)
13837-7	10036000138372	036000138375	42.86 x 25.72 x 14.67	1.392/1.81	E5	1.20 x 0.80 x 1.32	7 x 8 =56	0.30
13838-8	10036000138389	036000138382	42.86 x 25.72 x 14.67	1.596/2.04	E5	1.20 x 0.80 x 1.32	7 x 8 =56	0.40
13839-9	10036000138396	036000138399	42.86 x 25.72 x 14.67	1.8/2.25	E5	1.20 x 0.80 x 1.32	7 x 8 =56	0.40
13840-10	10036000138341	036000138405	42.86 x 25.76 x 14.67	1.992/2.44	E5	1.20 x 0.80 x 1.32	7 x 8 =56	0.45
13841-11	10036000138419	036000138412	42.86 x 25.76 x 14.67	2.196/2.51	E5	1.20 x 0.80 x 1.32	7 x 8 =56	0.46

### Product Description

KleenGuard® gloves are designed to protect hands against mechanical hazards, getting the job done where safety and flexibility is key. Each hand-specific pair of gloves is available in a choice of five sizes with colour-coded cuffs and roughened polyurethane coating for excellent grip. Seamless knitted nylon backing offers breathability and comfort. The gloves offer PPE category 2 protection for heavy-duty tasks in mechanical, manufacturing and construction environments, without breaking or tearing and still allowing sensitive touch for handling small parts. For other glove sizes, see product codes 13837, 13838, 13839 and 13840. 5 bags x 12 pairs hand specific, black gloves, 11, (120 total)

### Features and Benefits

Features	Benefits
<b>Dexterity</b>	Ideal for handling small components.
<b>High Tear &amp; Abrasion Resistance</b>	Reduced cost in use.
<b>Polyurethane Coating</b>	Excellent Grip due to roughened coating.
<b>Seamless Nylon Knit</b>	Breathability and comfort

# Product Data Sheet for KleenGuard® G40 Polyurethane Coated Gloves - Hand-Specific Pairs / Black

## Product Configuration

<b>Sterile</b>	No	<b>Latex Free</b>	No
<b>Main Protection Type</b>	General purpose	<b>Application</b>	Industrial
<b>Ambidextrous</b>	No	<b>Powdered</b>	No
<b>Material</b>	Other	<b>Coated</b>	Palm Coated
<b>Liner</b>	Seamless Knitted Nylon	<b>Coating</b>	Polyurethane
<b>Colour</b>	Black	<b>Chlorinated</b>	No
<b>Coating Type</b>	Smooth	<b>Gauge</b>	15
<b>Glove Shape</b>	Hand Specific	<b>Length</b>	220 - 260 mm

## International Standards and Symbols

### Solution

#### Safer Workplace

We know staff safety is your top priority. You can rely on our solutions to protect them, their environment and your important work.



#### Productive Workplace

The success of your business hinges on your work efficiency. That's why our solutions are designed to help improve your productivity.



### Standard R+E

#### CE Mark

Simple - CAT I, Intermediate - CAT II or Complex - CAT III



### Trade

#### ISO 9001

This gives the requirements for quality management systems, is now firmly established as the globally implemented standard for providing assurance about the ability to satisfy quality requirements and to enhance customer satisfaction in supplier-customer relationships.



### Packaging

<b>Unit Of Sale</b>	Case	<b>Max Weight(kg)</b>	2.76
<b>Case Dimension(LXWXH)(cm)</b>	42.86 x 25.76 x 14.67	<b>Inner Pack Material</b>	Cartonboard

### Instructions

The open book pictogram - indicates that the user should read and understand the USER INSTRUCTIONS before using the garment.

Protect from heat and radioactive sources.

Keep Dry. Store in a cool, dry place.

# Product Data Sheet for KleenGuard® G40 Polyurethane Coated Gloves - Hand-Specific Pairs / Black

## Information

It is the employer's responsibility to assess the risk of the task to be undertaken and determine the correct choice of personal protective equipment for the task. The manufacturer, Kimberly-Clark, does not accept any responsibility for the incorrect choice or misuse of the personal protective equipment shown in this brochure. All care has been taken to ensure that the information contained herein is as accurate as possible at the time of publication, however errors may occur and legislation concerning personal protective equipment is under constant review and may change in the lifetime of this brochure. Accordingly, the specification for the products may be subject to change. We would advise you to contact INFOFAX if you have any queries concerning the products shown or the suitability of such products for a particular task. Always dispose of used protective equipment in a safe and appropriate manner in accordance with European, National and Local environmental regulations.

<b>Websites</b>	<a href="http://www.kcprofessional.co.uk">www.kcprofessional.co.uk</a>	<b>Storage conditions</b>	Keep dry. Store in a cool dry place and shield from exposure to direct sunlight, intense artificial light or exposure to sources of radiation or ozone.
<b>Durability</b>	This product has a five years shelf life from the date of manufacture.		
<b>Customer Service Number</b>	For more information please contact Customer Service during regular office hours-0870 551 044		
<b>Country of Origin</b>	SRI LANKA		