

Plug FBS-SUB-9-GS-DP-B

Part number: 532216

FESTO



Data sheet

Feature	Value
Width	20 mm
Height	62 mm
Length	61 mm
Type code	FBS
Protocol	PROFIBUS
Control elements	DIL switch
Additional functions	Deactivation of forwarding bus segment
Product weight	60 g
Fieldbus interface	2x 2 spring-loaded terminals
Approved cable diameter	5 mm ... 10 mm
Degree of protection	IP65 IP67 In mounted state as per IEC 60529
Ambient temperature	0 °C ... 50 °C
Storage temperature	-20 °C ... 70 °C
Relative air humidity	95 % Non-condensing
Note on materials	RoHS-compliant
Housing material	PA-reinforced
Material of union nut	Brass
Material of screws	Steel
Seals material	NBR