



samlexamerica®

100A

Rackmount Switching Power Supplies

Model
SEC-100BRM
100 Amps



Design Features

- Voltage/Ampere meter
- Module status LEDs, fault indicator LEDs and fault alarm are standard features on all models
- Highly regulated output voltage
- Short circuit protection and overload current
- 25 pin D-sub connector for remote monitoring system

2 YEAR LIMITED WARRANTY

MODEL NO.	SEC-100BRM
NUMBER OF MODULES	5
INPUT VOLTAGE RANGE	105 to 125 VAC, 50 / 60 Hz
INPUT CURRENT	20 A
NOMINAL OUTPUT VOLTAGE	13.8 VDC
NO LOAD OUTPUT VOLTAGE	14 VDC
FULL LOAD OUTPUT VOLTAGE	13.35 VDC
OUTPUT REGULATION	1%
CONTINUOUS OUTPUT CURRENT	100 A
SURGE OUTPUT CURRENT	115 A
OUTPUT CURRENT LIMIT	120 A
MAXIMUM BATTERY CHARGING CURRENT	8 A
OUTPUT RIPPLE (PEAK TO PEAK)	150 mV
OUTPUT NOISE (PEAK TO PEAK)	0.7 V
COOLING	Forced air, 2 fans
PROTECTIONS	Short circuit, current limit, fan failure (LED and buzzer), input surge suppression
OPERATING TEMPERATURE	0 - 40° C
POWER CORD	12 AWG / 3 conductor
POWER CORD PLUG	125 V, 30 A, NEMA L5-30P, twist lock type
MODULE FUSE	250 V, 4 A
UNIT CIRCUIT BREAKER	125 / 250 V, 25 A
DIMENSIONS (19" Rack Mount, 2U height), MM (L x W x H)	483 x 404 x 91.4
DIMENSIONS (19" Rack Mount, 2U height), INCHES (L x W x H)	19 x 15.9 x 3.6
WEIGHT, KG	11.4
WEIGHT, LB	25.0

NOTE: Specifications are subject to change without notice

12001-SEC-100BRM-0715