

ELECTRONIC-SERVICE TOOL SETS

Special service sets for the maintenance and repairing of mobile phones and other high sensitive IT- instruments

The tools are clearly arranged in handy black imitation leather cases with zip fastener and velvet grey lining.

2251 Case with zip fastener, without tools

Outside dimensions: 190 x 135 x 35 mm (when closed)

2250 **BERNSTEIN** CARAT with tool set

9-piece set **conductive tools** from the series EUROline-Conductive, with bright-burnished, fine-polished pliers and bi-coloured conductive hand-guard, to meet the most exacting standards.

Weight with tools: approx. 0.360 g



2260 **BERNSTEIN** SELECT with tool set

9-piece set of tools from the series EUROline, with high quality tools

Weight with tools: approx. 0.360 kg

Tool set:

No.	Description of individual tools
3-651-14	EUROline-mini side cutters 120 mm, for copper wire up to 1.2 mm and soft wire up to 0.6 mm, fine polished - bright burnished, with bi-coloured hand-guard
3-683-14	EUROline-snipe nose pliers , 130 mm, plain jaws, bright burnished
4-161	Screwdriver for slotted screws , chrome vanadium, blade 40 x 1.0 mm, chrome plated, with special handle and swivel top
4-163	Screwdriver for slotted screws , chrome vanadium, blade 40 x 2.0 mm, chrome-plated, with special handle and swivel top
4-281	Cross-recess screwdriver , size 000, chrome vanadium, chrome-plated, with special handle and swivel top
4-283	Cross-recess screwdriver , size 0, chrome vanadium, chrome-plated, with special handle and swivel top
5-121	Engineer's tweezers , straight, round-pointed, 120 mm, nickel-plated
6-681	TORX-Screwdriver T 5 , chrome vanadium, chrome-plated, with special handle and swivel top
6-682	TORX-Screwdriver T 6 , chrome vanadium, chrome-plated, with special handle and swivel top

2270 **BERNSTEIN** ACCENT with tool set

9-piece set **conductive tools** with bright steel polished pliers and black, conductive hand-guard

Weight with tools: approx. 0.360 kg



Tool set:

No.	Description of individual tools
3-672-15	End cutters EUROline-Conductive , 130 mm, for copper wire up to 0.6 mm, fine polished - bright burnished
3-683-15	Snipe nose pliers EUROline-Conductive , 130 mm, plain jaws, fine polished - bright burnished
4-601	Screwdriver for slotted screws with conductive handle, chrome vanadium, chrome-plated, blade 50 x 0.8 mm
4-603	Screwdriver for slotted screws with conductive handle, chrome vanadium, chrome-plated, blade 50 x 1.5 mm
4-621	Cross-recess screwdriver , size 000, with conductive handle, chrome vanadium, chrome-plated
4-623	Cross-recess screwdriver , size 0, with conductive handle, chrome vanadium, chrome-plated
5-191	Tweezers made from conductive and acid-resistant black plastic, glassfibre reinforced
6-661	TORX-Screwdriver T 5 , with conductive handle, chrome vanadium, chrome-plated, with black tip
6-663	TORX-Screwdriver T 7 , with conductive handle, chrome vanadium, chrome-plated, with black tip



Tool set:

No.	Description of individual tools
3-601-13	Side cutter , 120 mm, for hard wire up to 0.4 mm and soft wire up to 1.0 mm
3-633-13	Snipe nose pliers , 120 mm, plain jaws
4-601	Screwdriver for slotted screws , with conductive handle, chrome vanadium, chrome-plated, blade 50 x 0.8 mm
4-603	Screwdriver for slotted screws , with conductive handle, chrome vanadium, chrome-plated, blade 50 x 1.5 mm
4-621	Cross-recess screwdriver , size 000, with conductive handle, chrome vanadium, chrome-plated
4-623	Cross-recess screwdriver , size 0, with conductive handle, chrome vanadium, chrome-plated
5-191	Tweezers made from conductive and acid-resistant black plastic, glassfibre reinforced
6-661	TORX-Screwdriver T 5 , with conductive handle, chrome vanadium, chrome-plated, with black tip
6-663	TORX-Screwdriver T 7 , with conductive handle, chrome vanadium, chrome-plated, with black tip