



19" LED Digital 12 Volt TV with Built-in Freeview T2 HD and DVD Player

- 19" HD widescreen LED TV
- Built-in Freeview T2 HD and Digital Freeview Channels
- Built-in DVD Player
- HDMI input for your external devices and consoles
- Can be wall mounted (100mm x 100mm)

	EAN	5060062269710
Specifications	Model No.	C1920FMTR
	Chipset	9206B
	Sales Market	UK
	VESA Size	100 x 100mm
	Wall Mount Screws	M4 x 8
	Speaker Output	2 x 3W
	Actual Size of Display (Diagonal)	18.5"

Display	Display Type	LED
	Resolution	1366 x 768 (16:9)
	Brightness (nit)	180
	Contrast	1000:1
	Display Colours	16.7M
	Refresh Rate	60Hz
	Viewing Angle H/V	178/178
	Reponse Time	14ms

Terminals	RF Antenna	2
	HDMI	x1
	CVBS	YES x 1(3.5 φ Mini Jack)
	PC In	x1
	Audio In	PC audio x 1(3.5 φ Mini Jack), CVBS Audio x1(Shared with Ypbpr)*
	Scart	x1
	YPbPr	YES x 1(3.5 φ Mini Jack)
	Digital Audio out	x1
	Earphone Out	x1
	USB on TV	x1
	CI	x1

Accessories	Remote	1
	Battery	AAA x 2

Features	DVB-S	With
	DVB-S2	With
	DVB-T+C	With
	DVB-T2+C	With
	CI	With
	3D Digital Comb Filter + 3D Noise Reduction	Yes
	Automatic Volume Control	Yes
	DVD	Yes
	Sleep Timer	Yes
	NO Signal Shut Down	Yes
	Adjustable Bass & Treble Controls	Yes
	Adjustable Balance Control	Yes
	Picture Modes	Standard/Dynamic/Soft/User
	Preset Sound Modes	Standard/Music/Movie/User
	OSD Menu Language	English/French/Spanish/Italy/Germany/Portugal
	Aspect Ratio Modes	Wide/Zoom/Cinema/Normal
PVR function	Recording standby, time-shift, EPG recording reservation	

Power	Power Supply	DC12V-3A /AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	17W
	KWh/annum	25kWh
	Max power Consumption	36W
	Standby Power Consumption	<0.5W
	Energy Efficiency Class	A

Dimensions	Unit Dimensions w Stand (mm)	446 x 160 x 323
	Unit Dimensions w/o Stand (mm)	446 x 69 x 285
	Weight (kg)	2.9