


RF / Coaxial Cable Assembly
IP67 SMA Bulkhead Jack-to-MCX Right Angle Plug, 100mm

multicomp PRO

**RoHS
 Compliant**

Electrical Performance:



Impedance	: 50Ω
Frequency Range	: DC ~ 6.0 Ghz
Working Voltage	: 170Vrms Max.
Dielectric Withstanding Voltage	: 750Vrms Max.
Insulator Resistance	: 1000MΩ Min.



Dimensions : Millimetres

Sl.	Description	Qty
1	SMA IP67 B/H Jack Crimp Type for OD 1.37mm cable	1
2	MCX R/A Plug Crimp for OD 1.37mm Cable	
3	1.37mm Black Cable	
4	Heat Shrink Tube F32 Ø2.5mm L=15mm Colour: Black	

Specification	DC ~ 6.0 GHz
VSWR	1.65 : 1 Max.
Insertion Loss	-1.5 dB Max.



Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO