


CLARITY A6

Bi-amplified 2-way studio monitor with 6,5" Woofer

The CLARITY A6 studio monitor is part of the new CLARITY Studio Monitor series and is an optimal solution for both home recording and the Studio. The technological implementation makes these Monitors ideal for high-level listening thanks to the linear frequency response and the possibility of adjustment for high and low frequencies. The wide choice of inputs positioned on the rear panel (XLR, TRS, RCA) guarantees ease of use. The modern and refined design and the satin black finish make this studio monitor elegant and suitable for many environments.

€ 201,00

including VAT



KEY FEATURES

Biamp two ways active speaker

60W RMS output power Woofer

30W RMS output power Tweeter

45Hz - 22KHz Frequency Response at -10dB

6.5" Woofer

1.0" Tweeter Silk Dome

Attenuation of High Frequencies (-2/-1/0/+1dB above 2KHz)

Attenuation of Low Frequencies (-2/-1/0/+2dB below 100Hz)

Balanced 1/4 "TS / XLR and unbalanced RCA inputs

Satin Black finish

Rugged MDF Case

MORE SPECIFICATIONS

Speaker Type	Biamp two ways active speaker
Mains Power	220-240V~/50-60Hz
Fuse	T5AL250V
Frequency response (-10dB)	45Hz- 22KHz
Woofer	6,5" (Paper Cone)
Tweeter	1,0" (Silk Dome)
Crossover	2.5KHz
Woofer Output Power	60W RMS
Tweeter Output Power	30W RMS
SPL (1m axial direction)	111dB
Audio Input Connections	Balanced type 1/4" / XLR interface, unbalanced RCA
High Frequency Adjustment	-2/-1/0/+1dB above 2KHz
Low Frequency Adjustment	-2/-1/0/+2dB below 100Hz
Cabinet Material	MDF
Dimensions(WxDxH)	224 x 253 x 350 mm
Weight	7,4Kg
Packing Dimensions(WxDxH)	265 x 325 x 410 mm
Packing Weight	6,5Kg