

TONE & PROBES



Tone Specifications (402T):

ELECTRICAL	
Output Power	pulsing 15dBm into 75Ω
	alternating 18dBm into 75Ω
Output Frequency	75KHz nominal
Voltage Protection	60V (in OFF position)
Allowable Attenuation	viable tone signal to 45dB
POWER SOURCE	
Battery	1 x 9V Battery
Battery Life	>25 hrs. nominal
ENVIRONMENT	
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-50°C to 75°C (-58°F to 167°F)
PHYSICAL	
Length	32 mm (1.25 inches)
Width	64 mm (2.5 inches)
Depth	57 mm (2.25 inches)
Weight	128 g (4.5 oz)
CONSTRUCTION	
	High impact ABS plastic
WARRANTY	
	1 year

Probe Specifications (402R):

ELECTRICAL	
Voltage Protection	50V (in OFF position)
POWER SOURCE	
Battery	1 x 9V
Battery Life	>50 hours (nominal)
Allowable Attenuation	Viable tone signal to 45dB
ENVIRONMENT	
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-50°C to 75°C (-58°F to 167°F)
PHYSICAL	
Length	229 mm (9.0 inches)
Width	54 mm (2.125 inches)
Height	28 mm (1.125 inches)
Weight	0.16 kg (0.34 lbs)
CONSTRUCTION	
	High Impact ABS Plastic
WARRANTY	
	1 year

Order Information:

CAT. NO.	DESCRIPTION
402K	CATV Cable Tone Test Set
402T	Transmitter
402R	Receiver

1390 Aspen Way Vista, CA • 92081 TC-402K 04/21

Latin America Phone : 1.760.510.0558 | EMEA Phone: +44 (0) 1633 927050
 ©2021 Tempo Communications Inc. • An ISO 9001 Company

EMEA Office: Tempo Europe Limited
 Brecon House, William Brown Close, Cwmbran • NP44 3AB, UK

TempoCom.com | tel 800.642.2155 | sales@tempocom.com



Renewed Vision. Innovation Forward.



Follow us on Social Media
 @TempoComms