

18V Blower BL LXT

DUB184RT

DUB184 is a cordless blower powered by 18V LXT Li-Ion battery



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Voltage	18 v
Battery Quantity (5.0ah)	1
Max air velocity	52.1 m/sec
Max air volume	13.0 m ³ /min
Noise sound pressure	86.6 dB(A)
Noise sound power	93.5 dB(A)
Noise K factor	2.7 dB(A)
No Load Speed	0 - 18,000 rpm
Vibration K factor	1.5 m/sec ²
Vibration no load	2.5 m/sec ²
Net weight	2.5 - 3.0 kg

USER BENEFITS

- Variable speed
- Brushless motor
- Lock-on function
- Cruise control function: Cruise control lever allows you to lock the variable speed control trigger at the desired power level.
- Constant speed control
- Best grip to frame angle provides optimum nozzle to ground angle for efficient sweeping operation

[Link to product - makita.com](https://www.makita.com)



RELATED PRODUCTS

(Reco

■ STANDARD ACCESSORIES

197282-4

Battery BL1850B 18v Li-ion



DC18RC

DC18RC COMPACT CHARGER



■ OTHER