

18V Linetrimmer BL LXT

DUR191LRT8

Cordless linetrimmer powered by 18V LXT Li-ion battery.

Split-shaft design

Supplied with nylon line head only.



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Voltage	18 v
Battery Quantity (5.0ah)	1
Noise sound pressure	77 dB(A)
Noise sound power	91.6 dB(A)
Noise K factor	3.9 dB(A)
Spindle Size	M10 x 1.25 L
Cutting diameter	300 mm
No Load Speed	3,500 / 5,100 / 6,000 rpm
Vibration K factor	1.5 m/sec ²
Vibration no load	2.5 m/sec ²
Net weight	3.2 - 3.5 kg

USER BENEFITS

- 2-Section Shaft for easy and space saving storage and transport
- Active Feedback Sensing Technology (AFT): Shuts down the tool if the rotation speed suddenly slows down
- Automatic Torque Drive Technology: Automatically changes the cutting speed according to load condition for optimum operation
- Brushless motor
- Electronic current limiter for overload protection.
- Electric brake
- Soft start feature.
- Constant speed control
- Reverse switch for easy removal of grass clippings stuck.
- Loop handle
- 3-Speed settings (Hi/Med/Low)

[Link to product - makitauk.com](https://www.makita.com)



RELATED PRODUCTS

(Recon

STANDARD ACCESSORIES

197282-4

Battery BL1850B 18v Li-ion



DC18RC

DC18RC COMPACT CHARGER



OTHER