



# 40Vmax Linetrimmer BL XGT

## UR003GD201

UR003G is a cordless Linetrimmer powered by 40Vmax XGT Li-ion battery



### TECHNICAL SPECIFICATIONS

No Load Speed (Med)	5,300 rpm
Battery Type	Lithium-ion
Voltage	40 v
Battery Quantity (2.5Ah)	2
Noise sound pressure	72.2 dB(A)
Noise sound power	89.7 dB(A)
Noise K factor	2.2 dB(A)
Spindle Size	M10 x 1.25 L
Cutting diameter	350 mm
No Load Speed (Hi)	6,500 rpm
No Load Speed (Lo)	3,500 rpm
Vibration K factor	1.5 m/sec <sup>2</sup>
Vibration no load	2.5 m/sec <sup>2</sup>
Net weight	4.5 – 4.8 kg

### USER BENEFITS

- Active Feedback Sensing Technology (AFT): Shuts down the tool if the rotation speed suddenly slows down
- Automatic Torque Drive Technology: Automatically changes the cutting speed according to load condition for optimum operation
- Brushless motor
- Electric brake
- Soft start feature.
- Constant speed control
- Reverse switch for easy removal of grass clippings stuck.
- Electronic 3-speed (Hi/Med/Lo)
- Small protector for better view of cutting area
- Extremely low noise
- Ergonomically designed loop handle with rubberised soft grip
- IPX4 level water resistant

[Link to product - makitauk.com](https://www.makita.com)



# RELATED PRODUCTS

(Recom

## STANDARD ACCESSORIES

### 191B36-3

BL4025 XGT 2.5AH 40v Max Li-ion



### 191C10-7

ADP10 XGT TO LXT CHARGER



### 191E08-6

DC40RA FAST CHARGER SET



## OTHER