

40Vmax BLOWER XGT

UB001GZ

UB001G is a cordless blower powered by 40Vmax XGT Li-Ion battery



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Voltage	40 v
Max air velocity	64 m/sec
Max air volume	16.0 m ³ /min
Noise sound pressure	83.7 dB(A)
Noise sound power	94.1 dB(A)
Noise K factor	3.2 dB(A)
No Load Speed	0 - 23,000 rpm
Vibration K factor	1.5 m/sec ²
Vibration no load	2.5 m/sec ²
Net weight	3.1 – 3.9 kg

USER BENEFITS

- Variable speed
- Cruise control function: Cruise control lever allows you to lock the variable speed control trigger at the desired power level.
- High air volume and speed delivered by brushless motor.
- Constant speed control
- Boost mode: 20N max blowing force is always available
- IPX4 Waterproof Design - resists splashing water
- 3-stage telescopic long nozzle
- Best grip to frame angle provides optimum nozzle to ground angle for efficient sweeping operation
- Lightweight & compact for single handed operation
- Low noise emissions
- Compatible with shoulder belt
- 12 minutes run time with 4.0Ah battery in cruise control mode.

[Link to product - makitauk.com](https://www.makita.com)



RELATED PRODUCTS

(Recon

■ OTHER