

# 40Vmax BLOWER XGT

## UB001GD201

UB001G is a cordless blower powered by 40Vmax XGT Li-Ion battery



### TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Voltage	40 v
Battery Quantity (2.5Ah)	2
Max air velocity	64 m/sec
Max air volume	16.0 m <sup>3</sup> /min
Noise sound pressure	83.7 dB(A)
Noise sound power	94.1 dB(A)
Noise K factor	3.2 dB(A)
No Load Speed	0 - 23,000 rpm
Vibration K factor	1.5 m/sec <sup>2</sup>
Vibration no load	2.5 m/sec <sup>2</sup>
Net weight	3.1 – 3.9 kg

### USER BENEFITS

- Variable speed
- Cruise control function: Cruise control lever allows you to lock the variable speed control trigger at the desired power level.
- High air volume and speed delivered by brushless motor.
- Constant speed control
- Boost mode: 20N max blowing force is always available
- IPX4 Waterproof Design - resists splashing water
- 3-stage telescopic long nozzle
- Best grip to frame angle provides optimum nozzle to ground angle for efficient sweeping operation
- Lightweight & compact for single handed operation
- Low noise emissions
- Compatible with shoulder belt
- 12 minutes run time with 4.0Ah battery in cruise control mode.

[Link to product - makitauk.com](https://www.makita.com)



# RELATED PRODUCTS

(Recom

## STANDARD ACCESSORIES

### 191B36-3

BL4025 XGT 2.5AH 40v Max Li-ion



### 191C10-7

ADP10 XGT TO LXT CHARGER



### 191E08-6

DC40RA FAST CHARGER SET



## OTHER