



40Vmax Hedgetrimmer 60cm XGT UH004GD202

Cordless Hedge Trimmer powered by 40Vmax Li-ion battery.



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Voltage	40 v
Blade Length	600 mm
Blade type	Double Sided
Max Branch Diameter	23.5 mm
Strokes per Minute	2,000 / 3,600 / 5,000 spm
Net weight	4.3 – 4.9 kg
Noise sound pressure	85 dB(A)
Noise sound power	96 dB(A)
Noise K factor	3 dB(A)
Vibration: Left Handle (Front grip)	2.9 m/sec ²
Vibration: Right Handle (Rear grip)	2.5 m/sec ²
Vibration K factor	1.5 m/sec ²
Battery Quantity (2.5Ah)	2

USER BENEFITS

- Brushless motor
- Constant speed control
- Electric brake
- Electronic 3-speed selection
- Reverse switch to free the blade when it is jammed by thick branches
- IPX4 level water resistant
- Sharp edge curved blade: ideal for trimming
- Inclined tooth edge enables the blade to easily catch, firmly hold and sharply cut twigs or thin branches
- Curved teeth reduce friction resistance to suppress energy loss
- Front handle switch
- Rubberised soft grip
- Low Vibration.

[Link to product - makita.com](https://www.makita.com)



RELATED PRODUCTS

(Recon

STANDARD ACCESSORIES

191B36-3

BL4025 XGT 2.5AH 40v Max Li-ion



191C10-7

ADP10 XGT TO LXT CHARGER



191E08-6

DC40RA FAST CHARGER SET



OTHER