

C-LED-HDMI1906D 18.5" MONITOR



Features:

- Industrial level LCD panel, suitable for continuous 24/7 operation
- Light and cost-effective plastic housing
- High fidelity digital processing for a brilliant and vivid video
- 5ms fast response time with no image blurring or ghosting
- Low energy consumption, long service life



Technical Specification

Model

Model	C-LED-HDMI1906D
-------	-----------------

Display

Screen Size	18.5"
Monitor Aspect Ratio	16:9
Resolution	1366x768
Backlight	LED
Brightness	200cd/m ²
Contrast Ratio	1000:1
Display Color	16.7M(8bit)
Viewing Angle(H/V)	90°(H)/65°(V)
Response time	5ms
Refresh Rate	60Hz

Signals

Port Input	HDMI×1, VGA ×1
------------	----------------

General

Power Supply	AC110~240V, 50/60 Hz
--------------	----------------------

Consumption (Standard)	25W	
Consumption (Standby)	<0.5W	
Type	Internal	
Net Weight	3.5kg (7.7lb)	
Gross Weight	4.3kg (9.5lb)	
Bezel Width	15.5mm(R/L), 17.5mm(U), 27mm(B)	
VESA	75x75mm (3.0"×3.0")	
Dimension without base (W×H×D)	442.0×276.0×51.5mm (17.4"×10.9"×2.0")	
Package(W×H×D)	492×385×113mm (19.4"×15.2"×4.4")	
Work Environment	Temperature	0°C~40°C (32°F~104°F)
	Humidity	10%~85%

Accessory

Standard	VGA cable, power cable, pedestal
Optional	Hanging bracket

Certifications

Certifications	CE/FCC
----------------	--------

Dimensions(mm)

