



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

### Features

#### Other

Applicator & Product Style	OCEAN
----------------------------	-------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1855639-1  
HDM/FA EAPR.130F.180F BENCH G /LM CUT



TE Part # 1855639-2  
HDM EAPR130F180F K



TE Part # 466092-1  
HDM EMPO130F180F LM



TE Part # 466092-2  
HDM EMPO130F180FK



TE Part # 466092-4  
HDM EMPR130F180F G



TE Part # 466124-3  
HDM EMPR100F180FK



TE Part # 466175-1  
HDM EMPO100F180FT



TE Part # 466175-3  
HDM EAPR100F180FK



TE Part # 466816-1  
HDM EMPR120F180FK



TE Part # 466881-2  
HDM EMPR090F180FK



TE Part # 680626-1  
HDM 8EMPO120F180F T&G



TE Part # 680868-2  
HDM 5EMPR090F180F K



TE Part # 687859-1  
HDM EMPO130F180FT



TE Part # 687859-2  
HDM EMPO130F180FK



TE Part # 687940-1  
HDM EMPO110F180F T & G



TE Part # 687948-1  
HDM EMPO100F180FT



TE Part # 687948-3  
HDM EMPR100F180FK



TE Part # 687949-4  
APPL,HDM 5EMPO110F180F G

## Customers Also Bought



## Documents

### Datasheets & Catalog Pages

#### CRIMPING WHERE FORM MEETS FUNCTION

English

### Instruction Sheets

#### Instruction Sheet (U.S.)

English