



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

### Features

#### Other

Applicator & Product Style	OCEAN
----------------------------	-------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




TE Part # 2836135-2  
OCEAN\_2.0\_APPLICATOR-S-033F055OA



TE Part # 2-2836135-2  
OCEAN\_2.0\_APPLICATOR-S-033F055OA



TE Part # 2836129-2  
OCEAN\_2.0\_APPLICATOR-S-033F055O



TE Part # 7-2836135-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-033F055O

## Customers Also Bought



TE Part #179228-3  
AMP COMMON TERMINATION HOUSINGS



TE Part #1969116-1  
187 & 250 FASTON HSG., REC., 3 POS, NATRUAL



TE Part #1744318-1  
Receptacle Housing: 2.54mm, 1 Row, CST-100 II




TE Part #2151011-1  
OCEAN\_2.0\_Applicator-S-042F070F



TE Part #1803095-3  
FLOATING SHEAR, FRONT



TE Part #1803224-9  
CRIMPER, WIRE F



TE Part #2-1333228-0  
ANVIL



TE Part #E94629-000  
RT-3-NO.1-0-1.5IN



TE Part #1338684-1  
SHEAR HOLDER, FRONT



TE Part #1490525-1  
DEPRESSOR, WIRE

## Documents

### Datasheets & Catalog Pages

CRIMPING WHERE FORM MEETS FUNCTION

English

### Instruction Sheets

Instruction Sheet (U.S.)



English