

**PRO COM IO-LINK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The power supply products can also be used universally in conjunction with our Industrial Ethernet, lightning and surge protection, relays and semiconductor switches, and can be combined to form many complete solutions.

**General ordering data**

Version	Communication module
Order No.	<a href="#">2587360000</a>
Type	PRO COM IO-LINK
GTIN (EAN)	4050118599152
Qty.	1 pc(s).

**PRO COM IO-LINK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	33.6 mm	Depth (inches)	1.323 inch
Height	74.4 mm	Height (inches)	2.929 inch
Width	35 mm	Width (inches)	1.378 inch
Weight	29 g	Net weight	29 g

**Temperatures**

Operating temperature	-25 °C...70 °C
-----------------------	----------------

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**General data**

MTTF	According to Standard	SN 29500
	Operating time (hours), min.	7.148 Mh
	Ambient temperature	40 °C
	Duty cycle	100 %
Operating temperature	-25 °C...70 °C	
Weight	29 g	

**Connection data (signal)**

Wire connection method	PUSH IN	Wire cross-section, AWG/kcmil , max.	16
Wire cross-section, AWG/kcmil , min.	26	Wire cross-section, solid , max.	1.5 mm <sup>2</sup>
Wire cross-section, solid , min.	0.14 mm <sup>2</sup>		

**Approvals**

Certificate no. (cULus)	E258476	Institute (cULus)	CULUS
-------------------------	---------	-------------------	-------

**Approvals**

Approvals



UL File Number Search	E258476
-----------------------	---------

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">declaration of conformity</a>
Engineering Data	<a href="#">STEP</a>
Software	<a href="#">IO-Link IODD für topGUARD</a> <a href="#">IO-Link IODD für PROtop</a>
User Documentation	<a href="#">Instruction sheet</a> <a href="#">IO-Link Register Description PROtop</a> <a href="#">Addressing and IO-Link Register Description topGUARD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

Creation date July 21, 2021 10:19:19 PM CEST

Catalogue status 16.07.2021 / We reserve the right to make technical changes.

**PRO COM IO-LINK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****Slotted screwdriver**

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

**General ordering data**

Type	SDIS SL 0.6X3.5X100	Version
Order No.	<a href="#">1274660000</a>	Screwdriver, Mounting tool
GTIN (EAN)	4050118072631	
Qty.	1 pc(s).	