



SANDFLEX® Bi-metal, 3830-C

SANDFLEX® holesaws in a new self-service packing.

Our SANDFLEX® holesaws work excellently in most materials such as wood, steel and metal. Fit all power drills, both stationary and portable. Knockout holes allow easy removal of cores. Cutting depth max.38 mm (1 1/2") 4/6 teeth per inch.
Max. holesize = nominal holesaw size +1,5 mm./ - 0,0.



3830-14-C	8228347	1	14	22
3830-16-C	8225353	1	16	22
3830-17-C	8228354	1	17	22
3830-19-C	8225360	1	19	30
3830-20-C	8225377	1	20	35
3830-21-C	8228361	1	21	45
3830-22-C	8225384	1	22	55
3830-24-C	8228378	1	24	60
3830-25-C	8225391	1	25	60
3830-27-C	8225407	1	27	60
3830-29-C	8225414	1	29	70
3830-30-C	8225421	1	30	75

3830-32-C	8225438	1	32	75
3830-33-C	8228385	1	33	75
3830-35-C	8225445	1	35	75
3830-37-C	8228392	1	37	75
3830-38-C	8225452	1	38	80
3830-40-C	8228408	1	40	90
3830-41-C	8225469	1	41	95
3830-43-C	8228415	1	43	105
3830-44-C	8225476	1	44	110
3830-46-C	8228422	1	46	115
3830-48-C	8225483	1	48	115
3830-50-C	8260873	1	50	120
3830-51-C	8225490	1	51	120
3830-52-C	8228439	1	52	120
3830-54-C	8225506	1	54	160
3830-55-C	8270919	1	55	160
3830-56-C	8228446	1	56	160
3830-57-C	8225513	1	57	170
3830-59-C	8228453	1	59	170
3830-60-C	8225520	1	60	180
3830-64-C	8225537	1	64	190
3830-65-C	8228460	1	65	190
3830-67-C	8225544	1	67	230
3830-68-C	8228477	1	68	230
3830-70-C	8225551	1	70	250

3830-73-C	8228484	1	73	250
3830-76-C	8225568	1	76	250
3830-79-C	8228491	1	79	250
3830-83-C	8225575	1	83	310
3830-86-C	8228507	1	86	310
3830-89-C	8225582	1	89	350
3830-92-C	8225599	1	92	380
3830-95-C	8225605	1	95	390
3830-98-C	8228514	1	98	420
3830-102-C	8225612	1	102	410
3830-105-C	8225629	1	105	460
3830-108-C	8228521	1	108	460
3830-111-C	8228538	1	111	460
3830-114-C	8225636	1	114	530
3830-121-C	8225643	1	121	600
3830-127-C	8225650	1	127	650
3830-133-C	8228545	1	133	650
3830-140-C	8228552	1	140	650
3830-146-C	8228569	1	146	650
3830-152-C	8225667	1	152	900



SANDFLEX® Bi-metal, 3830-VIP

Our SANDFLEX® Bi-metal holesaws work excellently in most materials such as wood, steel and metal. Fit all power drills, both stationary and portable. Knockout holes allow easy removal of cores. Cutting depth max.38 mm (1 1/2") 4/6 teeth per inch. All -VIP holesaws are packed in a cardboard box with an instruction leaflet enclosed.

Max. holesize = nominal holesaw size +1.5 mm./ - 0.0

Extra large sizes.

168 mm and 210 mm 6 TPI (R6). Cutting depth max. 38 mm. 177 mm 4/6 TPI.

Cutting depth max 50 mm.

All large holesaws cut with 0 degree cutting angle to be less aggressive.



3830-14-VIP	8041618	1	14	20
3830-16-VIP	8041625	1	16	20
3830-17-VIP	8041632	1	17	30
3830-19-VIP	8041649	1	19	30
3830-20-VIP	8041656	1	20	30
3830-21-VIP	8041663	1	21	40
3830-22-VIP	8041670	1	22	40
3830-24-VIP	8041687	1	24	55
3830-25-VIP	8041694	1	25	55
3830-27-VIP	8041700	1	27	70
3830-29-VIP	8041717	1	29	70

3830-30-VIP	8041724	1	30	70
3830-32-VIP	8041731	1	32	70
3830-33-VIP	8041748	1	33	70
3830-35-VIP	8041755	1	35	70
3830-37-VIP	8041762	1	37	80
3830-38-VIP	8041779	1	38	80
3830-40-VIP	8041786	1	40	80
3830-41-VIP	8041793	1	41	80
3830-43-VIP	8041809	1	43	90
3830-44-VIP	8041816	1	44	100
3830-46-VIP	8041823	1	46	100
3830-48-VIP	8041830	1	48	100
3830-50-VIP	8260866	1	50	120
3830-51-VIP	8041847	1	51	120
3830-52-VIP	8041854	1	52	120
3830-54-VIP	8041861	1	54	140
3830-55-VIP	8270902	1	55	160
3830-56-VIP	8152703	1	56	140
3830-57-VIP	8041878	1	57	140
3830-59-VIP	8041885	1	59	140
3830-60-VIP	8041892	1	60	160
3830-62-VIP	8234645	1	62	160
3830-64-VIP	8041908	1	64	180
3830-65-VIP	8041915	1	65	180
3830-67-VIP	8041922	1	67	200

3830-68-VIP	8196530	1	68	220
3830-70-VIP	8041939	1	70	220
3830-73-VIP	8041946	1	73	220
3830-76-VIP	8041953	1	76	240
3830-79-VIP	8041960	1	79	260
3830-83-VIP	8041977	1	83	260
3830-86-VIP	8041984	1	86	260
3830-89-VIP	8041991	1	89	270
3830-92-VIP	8042004	1	92	270
3830-95-VIP	8042011	1	95	270
3830-98-VIP	8042028	1	98	300
3830-102-VIP	8042035	1	102	320
3830-105-VIP	8042042	1	105	320
3830-108-VIP	8042059	1	108	350
3830-111-VIP	8042066	1	111	350
3830-114-VIP	8042073	1	114	360
3830-121-VIP	8042080	1	121	410
3830-127-VIP	8042097	1	127	520
3830-133-VIP	8042103	1	133	560
3830-140-VIP	8042110	1	140	560
3830-146-VIP	8042127	1	146	570
3830-152-VIP	8042134	1	152	610
3830-168	8040659	1	168	650
3830-177-HIGH	8101329	1	177	1340
3830-210	8040666	1	210	750



Holesaws Carbide tipped, 3832

Our Carbide Tipped holesaws work excellently in everything from bricks and ceramic tiles to such things as laminate, fibreglass and hardwood . Fit all power drills, both stationary and portable. Knockout holes allow easy removal of cores. Cutting depth 38 mm (1 1/2"), ground teeth, 4 teeth per inch. Max. holesize = nominal holesaw size +1,5 mm./ - 0,0.



3832-14	8557744	1	14	20
3832-16	8557768	1	16	20
3832-17	8557782	1	17	30
3832-19	8557805	1	19	30
3832-20	8557812	1	20	30
3832-21	8557829	1	21	40
3832-22	8557843	1	22	40
3832-24	8557867	1	24	55
3832-25	8557881	1	25	55
3832-27	8557904	1	27	70
3832-29	8557928	1	29	70
3832-30	8557942	1	30	70
3832-32	8557966	1	32	70
3832-33	8557980	1	33	70
3832-35	8558000	1	35	70

3832-37	8558024	1	37	80
3832-38	8558048	1	38	80
3832-40	8558062	1	40	80
3832-41	8558086	1	41	80
3832-43	8558109	1	43	90
3832-44	8558123	1	44	100
3832-46	8558147	1	46	100
3832-48	8558161	1	48	100
3832-51	8558185	1	51	120
3832-52	8558208	1	52	120
3832-54	8558222	1	54	140
3832-56	8558239	1	56	140
3832-57	8558246	1	57	140
3832-59	8558260	1	59	140
3832-60	8558284	1	60	160
3832-64	8558307	1	64	180
3832-65	8558321	1	65	180
3832-67	8558345	1	67	200
3832-68	8558352	1	68	220
3832-70	8558369	1	70	220
3832-73	8558383	1	73	220
3832-76	8558406	1	76	240
3832-79	8558420	1	79	260
3832-83	8558444	1	83	260
3832-86	8558468	1	86	260

3832-89	8558482	1	89	270
3832-92	8558505	1	92	270
3832-95	8558529	1	95	270
3832-98	8558543	1	98	300
3832-102	8558567	1	102	320
3832-105	8558581	1	105	320
3832-108	8558604	1	108	350
3832-111	8558611	1	111	350
3832-114	8558628	1	114	360
3832-121	8558642	1	121	410
3832-127	8558666	1	127	520
3832-133	8558673	1	133	560
3832-140	8558680	1	140	560
3832-146	8558697	1	146	570
3832-152	8558703	1	152	610