



Data sheet | Item number: 289-172

Interface module; RJ-45; RJ-45; Cat. 5; in mounting carrier


www.wago.com/289-172



Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at 01788 568 008.



Data

Electrical data

Operating voltage	\leq AC 30 V; \leq DC 42 V
Nominal current	1.5 A
Insulation resistance	\geq 500 M Ω

Safety and protection

Dielectric strength, contact/contact (AC, 1 min)	1 kV _{rms}
--	---------------------

Connection data

Pole No.	8
Connection type (1)	System
Pluggable connectors	RJ-45 (shielded)
Connection type 2	System
Pole number 2	8
Connector 2	RJ-45 (shielded)
Mating cycles	500
Transmission length (max.)	100 m
Connection cable	Cat. 5 (min.)

Subject to changes. Please also observe the further product documentation!



Physical data

Width	20.5 mm / 0.807 inch
Height	85 mm / 3.346 inch
Depth from upper edge of DIN-rail	51 mm / 2.008 inch

Mechanical data

Mounting type	DIN-35 rail
Housing design	Mounting carrier

Material data

Fire load	0.492 MJ
Weight	28.3 g

Environmental requirements

Surrounding air temperature (operation)	-40 ... 85 °C
Surrounding air temperature (storage)	-40 ... 85 °C
Surrounding air (operating) temperature for UL	-40 ... 70 °C
Relative humidity	85% (non-condensing)

Commercial data

Product Group	6 (Interface Electronics)
PU (SPU)	15 (1) Stück
Packaging type	box
Country of origin	DE
GTIN	4045454317478
Customs tariff number	85366990990

Subject to changes. Please also observe the further product documentation!