

# PH180 Waterproof pH Meter

**Flat surface electrode can measure solids, semi-solids, and liquids**

## Features:

- Measures from 0 to 14 pH with 0.01pH resolution
- Replaceable flat surface electrode makes it easy to wipe clean without damaging the electrode
- ATC (Automatic Temperature Control) compensates for temperature changes
- Dual display for pH and Temperature
- Analog bargraph for viewing trends
- 1-, 2-, or 3-point calibration
- CAL reminder after 15 on/off cycles
- RENEW warning when probe needs cleaning or replacement
- Auto power off (after 10 minutes) with disable
- Waterproof (IP57)
- Includes meter and electrode with protective cap, (4) CR2032 batteries, cup with cap and neckstrap

## Applications:

Easily measure solids, semi-solids and liquids in the lab or in the field.

## Specifications

pH Range	0 to 14pH
Accuracy	±0.01pH
Temperature Range	32 to 194°F (0 to 90°C)
Accuracy	±1.8°F/1°C
Calibration	1-, 2- or 3-point
Memory	25 readings
Power	(4) CR2032 batteries
Dimensions	7.8 x 1.5 x 1.5" (198 x 38 x 38mm)
Weight	3.5oz (100g)



## Ordering Information:

- PH180            Waterproof pH Pen  
PH185            Replacement Electrode for PH180

