



CorePro LEDcapsule LV

CorePro LEDcapsuleLV 2.7-28W G4 827

The CorePro LEDcapsule is a true alternative to the halogen capsule. It is particularly suitable for task lighting and decorative applications in homes, shops, hotels and restaurants. Compatible with existing fixtures with G4 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers significant energy savings and minimises maintenance costs without any compromise on light quality.

Product data

General Information		Operating and Electrical	
Cap base	G4 [G4]	Input frequency	- Hz
EU RoHS compliant	Yes	Power (Rated) (Nom)	2.7 W
Nominal lifetime (nom.)	15000 h	Lamp current (nom.)	340 mA
Switching cycle	50,000X	Wattage equivalent	28 W
Technical type	2.7-28W	Starting time (nom.)	0.5 s
		Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.65
		Voltage (Nom)	ac electronic 12 V
Light Technical		Temperature	
Colour Code	827 [CCT of 2,700 K]	T-Case maximum (nom.)	85 °C
Beam Angle (Nom)	300 °		
Luminous flux (nom.)	315 lm	Controls and Dimming	
Colour designation	Warm white (WW)	Dimmable	No
Correlated Colour Temperature (Nom)	2700 K	Mechanical and Housing	
Luminous efficacy (rated) (nom.)	116.00 lm/W	Bulb shape	Capsule
Colour consistency	<6		
Colour rendering index (nom.)	80		
LLMF at end of nominal lifetime (nom.)	70 %		

CorePro LEDcapsule LV

Lifetime



15K LED

15K LMP

