



<b>Order Code</b>	<b>TCK-151</b>
<b>Inductance</b>	4.7 $\mu$ H $\pm$ 20% (at 100 kHz / 300 mV)
<b>Impedance (DCR)</b>	150 m $\Omega$ max.
<b>Rated Current</b>	1.5 A max.
<b>Operating Temperature</b>	-40°C to +125°C



### Impedance Curve




### Outline Dimensions



#### Dimensions [mm]

<b>A</b>	3.0 $\pm$ 0.5
<b>B</b>	3.5 $\pm$ 0.5
<b>C</b>	2.1 $\pm$ 0.5
<b>D</b>	1.2 typ.
<b>E</b>	3.6
<b>F</b>	1.7
<b>G</b>	0.8



#### PCB PATTERN

