



Order Code	TCK-166
Inductance	8.2 μ H \pm 20% (100 kHz / 1 V)
Impedance (DCR)	27 m Ω max.
Rated Current	9 A max.
Operating Temperature	-55°C to +125°C



Impedance Curve



Outline Dimensions



Dimensions [mm]

Dimension	Value [mm]
A	10.0 \pm 0.3
B	10.0 \pm 0.3
C	4.0 max.
D	11.5 max.
E	2.0 \pm 0.3
F	3.0 \pm 0.3
G	5.4
H	13.6
I	4.1