



2-Port USB KVM Switch TK-207K

The 2-Port USB KVM Switch lets you manage two PCs with just one set of keyboard, monitor, and mouse. Switch between two PCs with a simple press of a button! Separate sets of KVM cables are included with the KVM Switch, so users can start controlling 2 PCs instantly. The KVM cables also provide power to the KVM Switch, eliminating the need for a power adapter. Hot Key operations provide immediate access to features such as computer switching, and auto-scanning. With its Hot-Plug, and Audible Feedback, the 2-Port USB KVM Switch is the perfect choice for managing multiple PCs.

FEATURES


- Use one keyboard, monitor, and mouse to control two computers
- USB Keyboard/Mouse emulation with 2-set of detachable KVM Cables
- Supports Microsoft Intellimouse, Optical Mouse, Logitech Net Mouse and more
- Supports super High Video Quality, up to 2048 x 1536 VGA resolution
- Supports Windows 98/98SE/ME/2000/XP/2003 Server, Linux, and Mac OS
- Multi-Platform support for PCs, Macintosh G3/G4, iMac and Mac Mini
- Hot-Plug pluggable. Adds PC or removes the connected PCs for maintenance without powering down the KVM Switch or other PC's.
- Switches PC by hot-keys, push button or windows-base client switch software.
- Auto-Scan & LED display for easy status monitoring
- User definable hot-key (Windows Only)
- USB Interface Power method
- 2-Year Limited Warranty

2-Port USB KVM Switch TK-207K

SPECIFICATIONS

Hardware	
Computer Connections	• 2
USB Interface	• USB 1.1 Specifications Compliant
KVM Cable	• 2 Sets of 1.2M (4ft) KVM Cables
Cable Interface	• To Console: 1 x VGA/SVGA HDB 15-pin (male) • To PC: 1 x USB (Type A), 1 x VGA/SVGA HDB 15-Pin (male)
Console Connectors	• 2 x USB Keyboard/Mouse: (Type A), 1 x VGA/SVGA 15-pin HDB
Port Selection	• Push Button, Hot-Key Commands, or Windows-Based Client Switching Software
Auto-Scan Interval	• 10 seconds
Display Data Channel (DDC)	• DDC2B DDC2AB
Keyboard State	• Saved and Restored
Power Type	• USB Interface Power
Dimensions	• 98 x 70 x 28 mm (3.86 x 2.76 x 1.1 in.)
Weight	• 99 g (3.4 oz)
Temperature	• Operating: 0°C ~ 40°C (32°F ~104°F) • Storage: -20°C ~ 60°C (-4°F ~140°F)
Humidity	• 0%~90%, Non-Condensing
Certifications	• CE, FCC

NETWORKING SOLUTIONS



PACKAGE CONTENTS

- TK-207K
- Multi-Language User's Guide
- 2 sets of USB KVM Cables

RELATED PRODUCTS

TK-205K	2-Port PS/2 KVM Switch
TK-208K	2-Port PS/2 Audio KVM Switch
TK-210K	2-Port USB Hub and PS/2 KVM Switch with Audio

ORDERING INFORMATION

TRENDnet®

20675 Manhattan Place, Torrance, CA 90501 USA
Tel: 1-310-961-5500
Fax: 1-310-961-5511
Web: www.trendnet.com
Email: sales@trendnet.com

To Order Please Call:

1-888-326-6061

