




DM800

VOCAL DYNAMIC MICROPHONE



Description

Specifically engineered for on stage performance, this mic offers flat and wide Frequency Response.

The cardioid polar pattern isolates the vocals from the background noise on stage or in studio.

Used on live or studio applications, the DM800 cardioid microphone is the right choice for clarity, resistance to feedback and ability to handle SPL without distortion.

- Vocal microphone with dynamic capsule
- Cardioid Polar Pattern
- Flat and extended Frequency Response
- ON/OFF switch
- Designed for optimal warmth and clarity
- Excellent accurate pickup pattern provides optimal gain before feedback
- 4.5 mt XLR cable included

Technical Specifications DM800

- Type Dynamic
- Polar Pattern Cardioid
- Frequency Response 60 - 14000 Hz
- Sensitivity -53 dB
- Max Spl for 1% THD 130 dB
- Impedance 600 Ω
- Connector 3 pin XLR male
- Weight 360 g
- Dimensions H 180 x O 45 mm