

ATP3X150 | ATP - PROTWIST® screwdrivers for Phillips® screws - round blades





Standards:

NF ISO 8764-1, NF ISO 8764-2, ISO 8764-1, ISO 8764-2, DIN ISO 8764-1, DIN ISO 8764-2, ASME B107.600

Description:

- Extra-long blade up to 400 mm for difficult and remote access.
- Inline Hardening Process – +50% Tip Life and +100% Bar Strength.
- Handle Material - Softer for more Comfort and still Chemical Resistant.
- Blade " tri-coating " treatment (Zinc-Nickel-Chromium) - 4x Corrosion Resistance.
- Handle 'Channel' - +10% Torque.
- Laser Marking - gives virtually Permanent Marking.
- CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.



	ATP3X150
Diameter [mm]	40.0
Diameter D1 [mm]	8.0
Length L1 [mm]	150.0
Length L [mm]	275.0
Length L2 [mm]	125.0
Weight [g]	194.0
Phillips Tip Number ["]	PH3