

ATD1X35 | ATD - PROTWIST® screwdrivers for Pozidriv® screws - short blades





Standards:

NF ISO 8764-1, NF ISO 8764-2, ISO 8764-1, ISO 8764-2, DIN ISO 8764-1, DIN ISO 8764-2, ASME B107.600

Description:

- Short round blade and ball handle for use in confined spaces.
- Inline Hardening Process – +100% Tip Life and +100% Bar Strength.
- Handle Material - Softer for more Comfort and still Chemical Resistant.
- Blade " tri-coating " treatment (Zinc-Nickel-Chromium) - 4x Corrosion Resistance.
- Handle 'Channel' - +10% Torque.
- Laser Marking - gives virtually Permanent Marking.
- CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.



|  | ATD1X35 |
|--|---------|
| Diameter [mm] | 36.0 |
| Diameter D1 [mm] | 4.5 |
| Length L1 [mm] | 35.0 |
| Length L [mm] | 91.0 |
| Length L2 [mm] | 56.0 |
| Pozidriv Tip Number ["] | PZ1 |
| Weight [g] | 40.0 |