

## ATD3X150 | ATD - PROTWIST® screwdrivers for Pozidriv® screws - round blades





### Standards:

NF ISO 8764-1, NF ISO 8764-2, ISO 8764-1, ISO 8764-2, DIN ISO 8764-1, DIN ISO 8764-2, ASME B107.600

### Description:

- Inline Hardening Process – +100% Tip Life and +100% Bar Strength.
- Handle Material - Softer for more Comfort and still Chemical Resistant.
- Blade " tri-coating " treatment (Zinc-Nickel-Chromium) - 4x Corrosion Resistance.
- Handle 'Channel' - +10% Torque.
- Laser Marking - gives virtually Permanent Marking.
- CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.



	<b>ATD3X150</b>
Diameter [mm]	40.0
Diameter D1 [mm]	8.0
Length L1 [mm]	150.0
Length L [mm]	275.0
Length L2 [mm]	125.0
Pozidriv Tip Number ["]	PZ3
Weight [g]	194.0