

## ATWDH3X150CK | ATWDH.CK - PROTWIST® SHOCK screwdriver for Pozidriv® screws





### Standards:

NF ISO 8764-1, NF ISO 8764-2, ISO 8764-1, ISO 8764-2, DIN ISO 8764-1, DIN ISO 8764-2, ASME B107.600

### Description:

- Impact Zone with Steel Strike - hexagonal blade with 73MO steel.
- Hexagonal blade with shoulder to take a wrench.
- Extra-long blade for use in confined spaces.
- Inline Hardening Process – +100% Tip Life and +100% Bar Strength.
- Handle Material - Softer for more Comfort and still Chemical Resistant.
- Golden electroplated Tip - 4x Corrosion Resistance.
- Handle 'Channel' - +10% Torque.
- Laser Marking - gives virtually Permanent Marking.
- CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.



	ATWDH3X150CK
Diameter [mm]	40.0
Diameter D1 [mm]	8.0
Length L1 [mm]	150.0
Length L [mm]	275.0
Length L2 [mm]	125.0
Weight [g]	211.0
Diameter D2 [mm]	12.0
Pozidriv Tip Number ["]	PZ3