


ATXP20X100 | ATXP - PROTWIST® screwdrivers for Torx Plus® screws



Description:

- Compliant with Torx Plus® specifications.
- Inline Hardening Process – +100% Tip Life and +100% Bar Strength.
- Handle Material - Softer for more Comfort and still Chemical Resistant.
- Blade " tri-coating " treatment (Zinc-Nickel-Chromium) - 4x Corrosion Resistance.
- Handle 'Channel' - +10% Torque.
- Laser Marking - gives virtually Permanent Marking.
- CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.



	ATXP20X100
A [mm]	3.84
Diameter D1 [mm]	4.0
Length L1 [mm]	100.0
Length L [mm]	220.0
Length L2 [mm]	120.0
Weight [g]	67.0
Resistorx Number ["]	IP20