

# Probe and Sensor Kit with Heavy Duty Thermocouples and Miniature Connectors

## TK Series



Rugged carrying case design features an extra large area for a handheld thermometer, in addition to space for extra wire and accessories. The high impact plastic case has a secure snap lock, and a built-in carrying handle.

HH84 handheld thermometer sold separately.

- ✓ **Attache Type and Rugged Carrying Case Styles**
- ✓ **Available in J, K or E Calibrations**
- ✓ **Features 7 Probes, Wire and Extension Cables**
- ✓ **Complete Assortment of Accessories**
- ✓ **Custom Foam Packaging**

### Each Kit Includes:

- ✓ SP-RL type roller surface probe, 1 each
- ✓ SP-RA type right angle surface probe, 1 each
- ✓ SP-SP type surface probe, 1 each
- ✓ SP-BW type beaded wire probe, 1 each
- ✓ Immersion probe with miniature connector, 0.8 mm (0.032") OD, 1 each
- ✓ Immersion probe with miniature connector, 1.6 mm (0.062") OD, 1 each
- ✓ Immersion probe with miniature connector, 3 mm (0.125") OD, 1 each
- ✓ SMPW miniature connectors, 2 pair
- ✓ PFA coated wire, 22 AWG stranded, with SMPW miniature connectors, 600 mm (2')
- ✓ PFA coated wire, 30 AWG solid, on spool, 600mm (2')
- ✓ RSC retractable cable (1' expands 5x), with SMPW miniature connectors
- ✓ SP-EH, 4" extension handle for surface probes, 1 each

### Model TK-1

Attache style case is compact, and provides a convenient means of taking thermocouples to the field.



TK-1 kit supplied with compact attache case.

### To Order

Model No.	Description
TK-1-(* )	Attache type kit
TK-2-(* )	Rugged carrying case kit

\* Specify calibration: **J, K or E.**

**Ordering Example:** TK-2-K, rugged carrying case Type kit, Type K calibration (CHROMEGA®-ALOMEGA®) with 7 thermocouple probes and accessories.