

PSI Displays Ltd




Suite C2, Butts Business Centre, Butts Road, Chiseldon, Swindon, Wiltshire, SN4 0PP. UK.

Tel: +44 (0) 1793 740456

e-mail: sales@psidisplays.co.uk Website www.psidisplays.co.uk

LCD COLOUR MONITOR Model No. LRM4521

4 Monitors x 4.0" TFT LCD Colour Monitors with Digital LED Backlight Panel, 2 x Composite Video Inputs, BNC. Video Output, BNC. – Single PSU connection, Metal Cased in 19" Rack Mounting. Other sizes available.



Main Features:

- Resolution: 960 x 240 - 230400 pixels.
- Picture Ratio: 4:3
- Brightness: 290 cd/m2 LED Back Light
- Contrast Ratio: 250:1
- Input: 2 x Composite Video. BNC on each Monitor.
- Video Output on each Monitor. BNC.
- LCD Panel Screen Protector.
- Individual controls for each monitor.
- Metal Cabinet finished in Black. 2U.
- Mounting: 19" Rack Mounting.
- Single 12volt Power connection.
- Rack Tilt 30°/30°.

The LRM4521 offers 4 Monitors of 4.0" TFT LCD in one rugged 19" rack mounting 2U high. With Digital LED Backlight panel, Active Matrix technology offering superb sharp and high contrast images. Individual On/Off switches, Brightness and Colour adjustments and V1/V2 switch for each monitor. Active Video output (loop through). 12volt operation via single power source. With universal application potential, the unit is ideal for surveillance systems, monitoring systems and multimedia video applications.

SPECIFICATIONS:

- Active area: 82.08 x 61.56 (WxH)mm. • 262K Colours. • PAL and NTSC Auto.
- Response Time: 3/7ms (Tr / Tf). • Viewing angle: Left/Right: 75°, Up: 60°. Down: 70°.
- Individual On/Off, Brightness, Colour and V1/V1 switch. • Dot Pitch: 0.264 x 0.171 (HxW)mm.
- Power Source: 12V DC, 540mA, 5.4 Watts approx. AC Adaptor:100-240V 50/60Hz 1.5Amps
- Dimensions: 489 x 87.88 x 61. 19" Rack by 2U High. Carton: 510 x 215 x 180. (WxHxD)mm.
- Weight: Unit: 1.49 Kgms, Carton: 2.55 Kgms. • Temp: Operation: 5°C~ 40°C, Storage: -20~ 80°.

Connections: Each Monitor: Video 1/2 In: BNC. Video Out: BNC.

Single DC input (powers all 4 monitors): 2.1mm socket. AC adaptor: IEC socket.

Standard accessories: AC adapter, AC Mains Lead.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO