

# PSI Displays Ltd




Suite C2, Butts Business Centre, Butts Road, Chiseldon, Swindon, Wiltshire, SN4 0PP. UK.

Tel: +44 (0) 1793 740456

e-mail: sales@psidisplays.co.uk Website www.psidisplays.co.uk

## LCD COLOUR MONITOR Model No. LM6323

5.6" Colour TFT LCD with LED Back light, Inputs of VGA, Composite Video x 2, Audio. Outputs: Composite Video, Audio via speaker & Headphones. Smart Metal Case with Sun visor.



### Main Features:

- Resolution: 960 x 234
- Picture Ratio: 4:3
- Brightness: 200 cd/m<sup>2</sup> LED Back Light.
- Contrast Ratio: 500:1
- Inputs: VGA, 2 x Composite, Audio.
- Output: Video and Audio via Speaker.
- Mounting: "C" mount. VESA 75mm.
- LCD Panel Screen Protector.
- Aluminium cabinet finished in Black.
- OSD Menu with Hot keys.
- Left/Right/Up/Down image reverse.

The LM6323 with TFT active matrix technology, offers a sharp and high contrast display with universal application opportunities. With a metal case it provides a rugged unit, Ideal for Surveillance Systems, Reverse Monitoring Vehicle systems and Video applications. Video image reverse Up/Down/Left/Right and Video Source hot keys. An audio input enables sound reception via speaker or Headphones. Sun Visor Hood and VESA 75x75mm Mounting. Note: The stand type may vary.

### SPECIFICATIONS:

- Active area: 112.896 x 84.672 (WxH)mm. • Dot Pitch: 0.0588 x 0.1764. • PAL and NTSC Auto.
- Response Time: 10/15ms (Tr/Tf). • Viewing angle: Left/Right: 70°, Up:50°, Down:70°.
- Controls: Menu, +, -, Image reverse, Source selection, On/off. Power On LED.
- Power Source: 12V DC, 500mAmp, 7 Watts approx.
- Dimensions: 169.4 x 136.2 x 36. Carton: 283 x 233 x 61 (WxHxD)mm.
- Weight: Unit: 0.82Kgms, Carton: 1.66Kgms. • Temp: Operation: -20°C~70°C, Storage: -30~80°C.

**Connections:** Input: VGA: 15 pin Sub-D, Video 1 & 2 Phono Socket, Audio Phono Socket. Output: Video Phono Socket. Audio via Headphone Jack: 3.5mm.

**Standard accessories:** AC Adaptor (UK), Desk/Wall Stand, Hood Visor.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO