


# PSI Displays Ltd



Suite C2, Butts Business Centre, Butts Road, Chiseldon, Swindon, Wiltshire, SN4 0PP. UK.  
Tel: +44 (0) 1793 740456  
e-mail: sales@psidisplays.co.uk Website www.psidisplays.co.uk

## LCD COLOUR MONITOR Model No. LM7327

7.0" TFT LCD Video Monitor Digital Colour LED Back Light, VGA, Composite video x 2, Metal Case, Sun Visor. Full OSD, Video out, Hot Keys, Audio. Other sizes available.



### Main Features:

- Resolution: 800xRGBx480 pixels.
- Picture Ratio: 16:9 & 4:3.
- Brightness: 185 cd/m2. LED Back Light.
- Contrast Ratio: 300:1
- Inputs: VGA, Composite Video x 2, Audio.
- Output: Composite Video, Audio via Speaker and Headphone.
- OSD Menu with Hot keys.
- Mounting: VESA 75x75mm and "C" mount.
- Aluminium cabinet finished in Black.
- LCD Panel Screen Protector.
- Hot Key: V1/V2/VGA and Image Reverse Left/Right/Up/Down.

The LM7327 with TFT active matrix technology, offers a sharp and high contrast display with universal application opportunities. Inputs of VGA, Composite Video and Audio, Metal cased with "C" and VESA mountings providing a rugged unit. Easy to setup and adjust with the Front panel keys and OSD. Hot Keys for Video image Up/Down/Left/Right and Video1/2. An audio input enables sound output via speaker or headphones. Ideal for Surveillance Systems, Reverse Monitoring Vehicle systems and Video and PC applications. Note: The Stand type may vary.

### SPECIFICATIONS:

- Active area: 154.08 x 85.92 (WxH)mm. • Dot Pitch: 0.073 x 0.219. • PAL and NTSC Auto.
- Response Time: 12/18ms (Tr/Tf). • Viewing angle: Left/Right: 70°, Up:50°, Down:70°.
- Controls: Menu, +, -, Left/Right/Up/Down image reverse, Video 1 & 2, On/off. Power On LED.
- Audio In and Out via Speaker and Headphone Jack. Video Output.
- Power Source: 12V DC, 266mA, 3.24 Watts approx.
- Dimensions: 195.7 x 136.2 x 36. Carton: 283 x 61 x 233 (WxHxD)mm.
- Weight: Unit:0.73Kgms, Carton: 1.56Kgms. • Temp: Operation: -10°C~60°C, Storage: -20~70°C.

**Connections:** Input: VGA: 15 pin D-SUB. Video 1 & 2: Phono Socket. Audio: Phono Socket. DC: 2.1mm jack Socket. Output: Video: Phono Socket. Audio via Headphone Jack: 3.5mm.

**Standard accessories:** Stand, UK AC Adaptor, Hood Visor.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO