

# KERN TB200-0.1US

Your reliable worktool for every day: light, easy, precise



## Construction

Cable length:	90 cm
Casing material:	Plastic
Dimensions (WxDxH):	161 x 69 x 32 mm
Dimensions housing (WxDxH):	161 x 69 x 32 mm
Overall dimensions mounted (WxDxH):	161 x 69 x 32 mm

## Piktogramme

### STANDARD



### OPTION



## Measuring system

Measuring head diameter:	8 mm
Precision (of [Max]):	0,500 %
Readability [d]:	100 $\mu$ m
Sound velocity (Max):	599940000 mm/min
Test frequency:	5 MHz
Weighing units:	inch mm

## Environmental conditions

Maximum operating temperature:	50 °C
Minimum ambient temperature:	0 °C

## Power supply

Battery:	4x1.5 V AA
----------	------------

## Services (optional)

Factory calibration certificate:	961-113
----------------------------------	---------

## Category

Brand:	Sauter
Category:	Material thickness gauges
Product Group:	Ultrasonic thickness gauge

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	265 x 215 x 63 mm
Gross weight:	958 g
Net weight:	292 g
Shipping method:	Parcel service