

KERN TC1250-0.1F

Your constant companion - compact and easy to use



Category

Brand:	Sauter
Category:	Coating thickness
Product Group:	Coating thickness gauge

Packaging & shipping


Delivery:	24 h
Dimensions packaging (WxDxH):	265 x 215 x 63 mm
Gross weight:	750 g
Net weight:	81 g
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions (WxDxH):	131 x 65 x 28 mm
Dimensions housing (WxDxH):	131 x 65 x 28 mm
Overall dimensions mounted (WxDxH):	131 x 65 x 28 mm

Piktogramme

STANDARD



OPTION



Measuring system

Measuring range [Max]:	100 x 1250 µm
Minimal base thickness:	300 µm
Precision (of [Max]):	3 %
Precision (Offset-Accur):	1 %
Readability [d]:	0 x 0,001 mm
Smallest sample surface, convex (radius):	1,500 mm
Smallest sample surface, flat (radius):	6 mm
Smallest sample surface,concave (radius):	2,500 cm
Weighing units:	µm inch (mil)

Display

Display digit height (large):	1 cm
-------------------------------	------

Environmental conditions

Maximum operating temperature:	50 °C
Minimum ambient temperature:	0 °C

Power supply

Battery:	4x1.5 V AAA
Operating time:	50 h

Services (optional)

Factory calibration certificate:	961-110
----------------------------------	---------