

KERN TDGOLD40

Ultrasound measuring instrument for testing the authenticity of gold and silver



Construction

Cable length:	90 cm
Casing material:	Plastic
Dimensions (WxDxH):	120 x 62 x 28 mm
Dimensions housing (WxDxH):	120 x 62 x 28 mm
Overall dimensions mounted (WxDxH):	120 x 62 x 28 mm

Piktogramme

STANDARD



OPTION



Measuring system

Measuring head diameter:	6 mm
Precision (of [Max]):	0,500 %
Readability [d]:	10 μ m
Sound velocity (Max):	599940000 mm/min
Sound velocity (Min):	60000000 mm/min
Test frequency:	5 MHz
Weighing units:	inch mm

Display

Display digit height (large):	1,800 cm
-------------------------------	----------

Environmental conditions

Maximum operating temperature:	50 °C
Minimum ambient temperature:	0 °C

Power supply

Battery:	4x1.5 V AAA
----------	-------------

Services (optional)

Factory calibration certificate:	961-113
----------------------------------	---------

Category

Brand:	Sauter
Category:	Material thickness gauges
Product Group:	Ultrasonic thickness gauge

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	265 x 215 x 63 mm
Gross weight:	750 g
Net weight:	164 g
Shipping method:	Parcel service