

# KERN FL 500G

Electronic tombstone tester for professional applications



## Measuring system

Measuring capacity [Max]:	500 N
Overload protection (of [Max]):	120 %
Precision (of [Max]):	0,200 %
Preset unit:	N
Readability [d]:	0,200 N
Test frequency:	1000 Hz

## Display

Display digit height (large):	8,500 mm
-------------------------------	----------

## Functions

Data hold function:	yes
Display revolving:	yes
Function to set limits:	yes
Peak function:	yes

## Environmental conditions

Maximum operating temperature:	35 °C
Minimum ambient temperature:	15 °C

## Power supply

Charging time:	8 h
Input voltage:	100 V - 240 V
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH
Operating time (Backlight off):	10 h
Operating time (Backlight on):	8 h

## Services (optional)

DAkkS Calibration certificate (Pressure):	963-261
DAkkS Calibration certificate (Tensile):	963-161
DAkkS Calibration certificate (Tensile/Pressure):	963-361

Factory calibration certificate:	961-361
Factory calibration certificate (Pressure):	961-261
Factory calibration certificate (Tensile):	961-161
Factory calibration certificate (Tensile/Pressure):	961-361

## Category

Brand:	Sauter
Category:	Force gauges

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	345 x 295 x 89 mm
Gross weight:	1,386 kg
Net weight:	515 g
Shipping method:	Parcel service
UN number:	3496

## Construction

Casing material:	Metal lacquered
Dimensions housing (WxDxH):	175 x 75 x 30 mm
Dimensions of display device (WxDxH):	175 x 75 x 30 mm
Overall dimensions mounted (WxDxH):	175 x 75 x 30 mm

## Piktogramme

### STANDARD



### OPTION

