

KERN MAP130K1

Hand grip dynamometer, e. g. for rehabilitation treatment after accidents



Construction

Dimensions device (WxDxH): 55 x 102 x 212 mm

Piktogramme

STANDARD



OPTION



Measuring system

Readability [d]:	100 g
Weighing capacity [Max]:	130 kg
Weighing units:	lb kg

Display

Display digit height (large):	1,100 cm
-------------------------------	----------

Environmental conditions

Maximum operating temperature:	35 °C
Minimum operating temperature:	5 °C

Power supply

Battery:	CR2450
Operating time:	53 h

Services (optional)

Factory calibration certificate:	961-167
----------------------------------	---------

Category

Brand:	KERN
Category:	Hand grip dynamometers

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	367 x 285 x 100 mm
Gross weight:	1,800 kg
Net weight:	336 g
Shipping method:	Parcel service
UN number:	3091