

KERN HO10K

Premium UCI hardness testing device for Rockwell, Brinell and Vickers



Construction

Casing material:	Metal lacquered
Dimensions (WxDxH):	28 x 83 x 160 mm
Dimensions housing (WxDxH):	28 x 83 x 160 mm
Overall dimensions mounted (WxDxH):	28 x 83 x 160 mm

Piktogramme

STANDARD



OPTION



Measuring system

Weighing units:	HV MPa HL HRC HRB HB
-----------------	----------------------

Functions

All measurement directions possible (360°):	yes
Function to set limits:	yes
Obtaining average:	yes
Statistical function:	yes
Visual ready signal:	yes

Power supply

Charging time:	8 h
Input voltage:	110 - 240 V
Mains adapter/adaptor included:	EURO
Operating time (Backlight off):	12 h
Operating time (Backlight on):	6 h

Services (optional)

Factory calibration certificate:	961-270
----------------------------------	---------

Category

Brand:	Sauter
Category:	Hardness testers

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	395 x 315 x 140 mm
Gross weight:	5 kg
Net weight:	500 g
Shipping method:	Parcel service
UN number:	3481