

KERN SW2000

Professional sound level meters of class I and class II in premium quality

KERN®



Category

Brand:	Sauter
Category:	Sound level meters
Product Group:	Sound level meter

Packaging & shipping


Delivery:	24 h
Dimensions packaging (WxDxH):	350 x 280 x 90 mm
Gross weight:	1,300 kg
Net weight:	700 g
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions device (WxDxH):	300 x 80 x 36 mm
Dimensions housing (WxDxH):	300 x 80 x 36 mm
Overall dimensions mounted (WxDxH):	300 x 80 x 36 mm

Piktogramme

STANDARD



OPTION



Measuring system

Measuring capacity [Max]:	136 db
Readability [d]:	0,100 db
Weighing units:	dB

Functions

Data hold function:	yes
Function to set limits:	yes
Peak function:	yes
Visual ready signal:	yes

Environmental conditions

Maximum operating temperature:	50 °C
Minimum operating temperature:	-10 °C

Power supply

Battery:	4x1.5 V AA
Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO
Operating time:	10 h

Services (optional)

DAkkS Certificate:	963-281
Factory calibration certificate:	961-281