



Make It Yours.

CK530 V2

CK-530-GKTR1-** / CK-530-GKTM1-** / CK-530-GKTL1-**

NO-NONSENSE PERFORMANCE



Get a straightforward keyboard that performs well on the battlefield with the CK530 V2 Gaming Mechanical Keyboard. A portable, tenkeyless format allows you to take your gear without sacrificing features or performance. Mechanical switches rated for 50 million clicks will guarantee your keyboard will stay combat-ready during all your long-lasting skirmishes. On-the-Fly Controls allow customization of your settings like RGB lighting and macros in real time, while software lets you get even further customization. The included wrist rest will ensure you stay comfortable during long gaming sessions. Simply put, the CK530 V2 is a capable tool that gets the job done.

FEATURES

- **Brushed Aluminum Design** - Curved top plate, floating keycaps, and minimalistic design built with functionality in mind
- **Mechanical switches** - Rated for a 50 million+ lifespan to never let you down in the heat of battle.
- **RGB Backlighting** - Per-key LEDs with multiple lighting modes and effects to highlight all your dominating killstreaks.
- **On-the-Fly Controls** - Make real-time adjustments to lighting and macros with no software necessary, including Windows Lock On/Off to prevent getting kicked out of the game when the Windows Key is accidentally pressed.
- **Easy-to-use Software** - Map 16.7 million colors to any key, customize lighting modes, and fine-tune macros
- **Hybrid Key Rollover** - Automatic switching between 6KRO and NKRO to ensure legacy compatibility and that always every press is registered.
- **Standard Layout** - For enthusiasts interested in custom keycaps, the CK530 V2 comes in standard size layout and standard bottom row.
- **Wrist Rest** - low-friction cloth for anti-irritation to keep you comfortable during long gaming sessions.

SPECIFICATIONS & PACKING INFORMATION

Product Name	CK530 V2
Product Number	CK-530-GKTR1-** (Red switch) CK-530-GKTL1-** (Blue Switch) CK-530-GKTM1-** (Brown switch)
Switch Type	Mechanical Switch
Material	Plastic / Aluminum
Color	Gunmetal Black
Keycap	Part of Asia/US layout: ABS Double-injection keycaps Other layouts: ABS Painting & Laser-engraved keycaps
LED Color	RGB
Polling Rate	1000 Hz
Response Rate	1ms / 1000Hz
MCU	32bit ARM Cortex M3
On board Memory	512KB
On-the-fly system	Yes, for Multi-media, Macro Recording and Lighting control
Multi-media Keys	Through FN
Smart cable manager	N/A
Wrist rest	YES
Cable	Fixed Rubberized 1.8m
Software Support	Yes, MasterPlus
Connector Cable	USB 2.0
Cable Length	1.8m
Dimensions	380* 135* 40mm (L*W*H)
Product Weight (without cable)	739g
Warranty	2 years

Net weight	739g
Gross weight	1170g
Package Dimensions (L x W x H)	391* 250* 48mm (L*W*H)
Carton dimension (L x W x H) / Units	535 * 410 * 270 mm (L*W*H) 10

Cont.	W/ Pallet	Carton/ Pallet	W/O Pallet
20'	2800 pcs	28 carton	N/A
40'	6720 pcs	28 carton	N/A
40 HQ	7680 pcs	32 carton	N/A

Wrist Rest	Specs
Materials	Base: Styrene-butadiene Rubber Surface: Jersey Cloth
Thickness	15mm
Surface Color	Black
Base Color	Black
Size	380 X 95 X 15 mm

FEATURE HIGHLIGHT



Mechanical Switches - Durable switches rated for 50 million clicks



RGB Backlighting - Per-key LEDs with multiple lighting modes and effects to highlight all your dominating killstreaks



Brushed Aluminum Design - Curved top plate, floating keycaps, and minimalistic design built with functionality in mind



Wrist Rest - low-friction cloth for anti-irritation to keep you comfortable during long gaming sessions.



Make It Yours.

EAN & UPC INFORMATION

Itemcode	EAN	UPC
CK-530-GKTL1-AE	4719512102046	884102074349
CK-530-GKTL1-AF	4719512102169	884102074462
CK-530-GKTL1-DE	4719512101803	884102074103
CK-530-GKTL1-FR	4719512101810	884102074110
CK-530-GKTL1-HE	4719512102138	884102074431
CK-530-GKTL1-HU	4719512102053	884102074356
CK-530-GKTL1-IT	4719512101827	884102074127
CK-530-GKTL1-JP	4719512102145	884102074448
CK-530-GKTL1-KR	4719512102152	884102074455
CK-530-GKTL1-ND	4719512101834	884102074134
CK-530-GKTL1-PT	4719512102060	884102074363
CK-530-GKTL1-RU	4719512102077	884102074370
CK-530-GKTL1-SP	4719512102084	884102074387
CK-530-GKTL1-SW	4719512102091	884102074394
CK-530-GKTL1-TA	4719512102107	884102074400
CK-530-GKTL1-TC	4719512102114	884102074417
CK-530-GKTL1-TU	4719512102121	884102074424
CK-530-GKTL1-UK	4719512101797	884102074097
CK-530-GKTL1-US	4719512101896	884102074196
CK-530-GKTM1-AE	4719512102176	884102074479
CK-530-GKTM1-AF	4719512102299	884102074608
CK-530-GKTM1-DE	4719512101841	884102074141
CK-530-GKTM1-FR	4719512101858	884102074158
CK-530-GKTM1-HE	4719512102268	884102074561
CK-530-GKTM1-HU	4719512102183	884102074486
CK-530-GKTM1-IT	4719512101865	884102074165
CK-530-GKTM1-JP	4719512102275	884102074585
CK-530-GKTM1-KR	4719512102282	884102074592
CK-530-GKTM1-ND	4719512101872	884102074172
CK-530-GKTM1-PT	4719512102190	884102074493
CK-530-GKTM1-RU	4719512102206	884102074509
CK-530-GKTM1-SP	4719512102213	884102074516
CK-530-GKTM1-SW	4719512102220	884102074523
CK-530-GKTM1-TA	4719512102237	884102074530
CK-530-GKTM1-TC	4719512102244	884102074547
CK-530-GKTM1-TU	4719512102251	884102074554
CK-530-GKTM1-UK	4719512101889	884102074189
CK-530-GKTM1-US	4719512101919	884102074219
CK-530-GKTR1-AE	4719512102305	884102074615
CK-530-GKTR1-AF	4719512102428	884102074738
CK-530-GKTR1-DE	4719512101742	884102074042
CK-530-GKTR1-FR	4719512101766	884102074066
CK-530-GKTR1-HE	4719512102398	884102074707
CK-530-GKTR1-HU	4719512102312	884102074622
CK-530-GKTR1-IT	4719512101780	884102074080
CK-530-GKTR1-JP	4719512102404	884102074714
CK-530-GKTR1-KR	4719512102411	884102074721
CK-530-GKTR1-ND	4719512101773	884102074073
CK-530-GKTR1-PT	4719512102329	884102074639
CK-530-GKTR1-RU	4719512102336	884102074646
CK-530-GKTR1-SP	4719512102343	884102074653
CK-530-GKTR1-SW	4719512102350	884102074660
CK-530-GKTR1-TA	4719512102367	884102074677
CK-530-GKTR1-TC	4719512102374	884102074684
CK-530-GKTR1-TU	4719512102381	884102074691
CK-530-GKTR1-UK	4719512101759	884102074059
CK-530-GKTR1-US	4719512101902	884102074202

Blue Switch

Brown Switch

Red Switch