


PORTABLE TANK HEATER

CH-OTS Series


- ✓ Copper Sheath Nickel Plated Elements
- ✓ High Watt Density (49 to 58 W/in²)
- ✓ 4 and 6 kW
- ✓ 208 and 240V, Single Phase

FEATURES

- ✓ 660 mm (26") Riser (Unheated Section)
- ✓ Integral Control 16 to 121°C (60 to 250°F)
- ✓ Manual Reset Cutout (Set @ 50°F Above Temperature Setpoint)
- ✓ Built-In Pilot Light
- ✓ 914 mm (36") Long Cord with 10 to 30P Plug



CH-OTS-404/240V, shown smaller than actual size.



To Order

kW	Volts	W/in ²	Phase	DIM B (inch)	Copper	Wt (lb)
					Model No.	
4	240	49	1	14	CH-OTS-404/240V	10
6	208	58	1	17	CH-OTS-608/208V	10
6	240	58	1	17	CH-OTS-604/240V	10

Ordering Example: CH-OTS-608/208V, 208V, 6 kW, 1 phase portable tank heater.