

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1122171024](#)
Status: **Active**
Overview: [Woodhead ArcArrest Connector System](#)
Description: Woodhead ArcArrest Plug with Handle, Drawplates, and Cap, Switch-Rated, 60.0A, 480V AC, 3-Pole+Ground, Insulator Keying Position 4, Three Grommets Included

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

UL E145922

General

Product Family Wiring Devices
 Series [112217](#)
 IP Rating IP69K
 NEMA Configuration N/A
 Overview [Woodhead ArcArrest Connector System](#)
 Product Name ArcArrest
 Receptacle Type N/A
 Specialty Switch-Rated
 Type Plug
 UPC 78172558660
 Wire Size AWG 4 to 8

Physical

Cord Grip Body Size F5 1 1/4"
 Flange Yes
 Flip Lid No
 Gender Male
 Length 178.99mm (7.047")
 Locking Blade N/A
 Poles 3

Electrical

Cord Type N/A
 Current - Maximum per Contact 60.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 480V AC

Material Info

Engineering Number ARC60MHDE03

Reference - Drawing Numbers

Sales Drawing 1122171024-000



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[112217 Series](#)