

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1122170024](#)  
**Status:** **Active**  
**Overview:** Woodhead ArcArrest Connector System  
**Description:** Woodhead ArcArrest Receptacle with Handle and Drawplates, Switch-Rated, 60.0A, 480V AC, 3-Pole+Ground, Insulator Keying Position 4, Three Grommets Included

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Brochure \(PDF\)](#)

**Agency Certification**

UL E145922

**General**

Product Family Wiring Devices  
 Series [112217](#)  
 IP Rating IP69K  
 NEMA Configuration N/A  
 Overview [Woodhead ArcArrest Connector System](#)  
 Product Name ArcArrest  
 Receptacle Type Single  
 Specialty Switch-Rated  
 Type Receptacle  
 UPC 78172558674  
 Wire Size AWG 4 to 8

**Physical**

Cord Grip Body Size F5 1 1/4"  
 Flange Yes  
 Flip Lid Yes  
 Gender Female  
 Length 199.08mm (7.838")  
 Locking Blade N/A  
 Poles 3

**Electrical**

Cord Type N/A  
 Current - Maximum per Contact 60.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 480V AC

**Material Info**

Engineering Number ARC60FHDE03

**Reference - Drawing Numbers**

Sales Drawing 1122170024-000



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[112217 Series](#)